

# LED Lighting for Roam Carts and Evolve Cabinets

Cabinet and cart interiors with LED lights improve visibility to supplies in departments throughout a hospital and are especially useful in hybrid ORs with dimmed overhead lighting. The LED

interior lighting can be installed on all Roam carts and Evolve tall, upper, and scope cabinets with hinged doors. They cannot be installed on Evolve upper cabinets with sloped tops.



- Lights run from the base to the top of the cabinet or cart.
- LEDs remain lit. Our customer service representatives can work with you to provide a custom solution that allows you to turn the lights on and off.
- The power cord is 10' long; it is not plenum rated.
- Power entry on Roam carts is on the back of the cart top.
- Power entry on Evolve cabinets is through the cabinet top.

## Lighting Details

- LED color - Cool White 6000k
- Average lifespan - 50,000 hours
- UL listed
- RoHS compliant
- Each cart or cabinet with LED lights requires 1 3-prong outlet. LED lights cannot be linked together.
- Input voltage - 12VDC or 24VDC
- Output voltage - 12VDC or 24VDC
- Output current - 5A @ 12VDC or 2.5A @ 24VDC

## Power Consumption

Product	Total power consumption (watts)
Roam 1 carts .....	16
Roam 2 carts .....	16
Roam 3 carts .....	32
Roam 4 carts .....	32
Evolve tall and upper cabinets .....	20
Evolve scope cabinets .....	22